

150KVA Transformer

45KVA-500KVA

PART NUMBER: TF-150KVA480/208SDC-M/F

PRODUCT DESCRIPTION:

150KVA Trystar Portable Transformer

480V:208Y/120V Step Down

UL 1640 Listed

C(ETL) Listed

UL 50 Listed

NEMA 3R

PRIMARY SIDE:

4- Wire Camlok Input (Brown, Orange, Yellow, Green)

225A 3P Primary Side Transformer Circuit Breaker

SECONDARY SIDE:

400A 3P 240V Secondary Side Transformer Circuit Breaker

2 Sets of 5- Wire Camlok Output (Black, Red, Blue, White, Green)

STANDARD FEATURES:

All Aluminum Corrosion Resistant Construction

Removable Gland Plates to Allow On Site Receptacle Changes

Heavy Duty Lifting Eyes and Industrial Casters

Powder Coat Color: Customer Choice

UV Print: Customer Logo

Made in the USA



***MULTIPLE CONFIGURATIONS: CONTACT TRYSTAR FOR MORE INFORMATION**