






4

3

2

1

| REVISIONS |      |                 |            |          |
|-----------|------|-----------------|------------|----------|
| ZONE      | REV. | DESCRIPTION     | DATE       | APPROVED |
|           | A    | INITIAL RELEASE | 10/11/2018 |          |
|           | B    | DIM LAYOUT      | 11/21/2018 |          |
|           | C    | POLARITY CHANGE | 12/4/2018  |          |



**PROPRIETARY AND CONFIDENTIAL**  
THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF OZTEK CORP. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF OZTEK CORP IS PROHIBITED.

|             |         |   |      |          |      |    |       |      |     |       |      |      |   |      |  |      |      |
|-------------|---------|---|------|----------|------|----|-------|------|-----|-------|------|------|---|------|--|------|------|
|             |         | UNLESS OTHERWISE SPECIFIED:<br><br>DIMENSIONS ARE IN MM<br>TOLERANCES:<br><table><tr><td></td><td>MM</td><td>INCH</td></tr><tr><td>.X</td><td>± .38</td><td>.020</td></tr><tr><td>.XX</td><td>± .12</td><td>.010</td></tr><tr><td>.XXX</td><td>±</td><td>.005</td></tr></table> ANGULAR: ± .5 DEG<br><br>USE MIN BEND RADII |      | MM       | INCH | .X | ± .38 | .020 | .XX | ± .12 | .010 | .XXX | ± | .005 |  | NAME | DATE |
|             | MM      |   | INCH |          |      |    |       |      |     |       |      |      |   |      |  |      |      |
| .X          | ± .38   |   | .020 |          |      |    |       |      |     |       |      |      |   |      |  |      |      |
| .XX         | ± .12   |   | .010 |          |      |    |       |      |     |       |      |      |   |      |  |      |      |
| .XXX        | ±       |   | .005 |          |      |    |       |      |     |       |      |      |   |      |  |      |      |
|             |         | DRAWN   | AGP  | 10/11/18 |      |    |       |      |     |       |      |      |   |      |  |      |      |
|             |         | CHECKED   | KWE  |          |      |    |       |      |     |       |      |      |   |      |  |      |      |
|             |         | ENG APPR.   |      |          |      |    |       |      |     |       |      |      |   |      |  |      |      |
|             |         | MFG APPR.   |      |          |      |    |       |      |     |       |      |      |   |      |  |      |      |
|             |         | Q.A.  |      |          |      |    |       |      |     |       |      |      |   |      |  |      |      |
|             |         | COMMENTS:   |      |          |      |    |       |      |     |       |      |      |   |      |  |      |      |
|             |         | MATERIAL  |      |          |      |    |       |      |     |       |      |      |   |      |  |      |      |
|             |         | FINISH  |      |          |      |    |       |      |     |       |      |      |   |      |  |      |      |
| NEXT ASSY   | USED ON |   |      |          |      |    |       |      |     |       |      |      |   |      |  |      |      |
| APPLICATION |         | DO NOT SCALE DRAWING  |      |          |      |    |       |      |     |       |      |      |   |      |  |      |      |



OZTEK CORP  
11 CONTINENTAL BLVD  
MERRIMACK, NH 03054

TITLE:  
**MUSTANG MECHANICAL  
OUTLINE DRAWING**


|                  |                       |                 |
|------------------|-----------------------|-----------------|
| SIZE<br><b>B</b> | DWG. NO.<br>DWG-00032 | REV<br><b>C</b> |
| SCALE: 1:6       | WEIGHT:               | SHEET 1 OF 2    |

4


3

2

1



**PROPRIETARY AND CONFIDENTIAL**  
THE INFORMATION CONTAINED IN THIS  
DRAWING IS THE SOLE PROPERTY OF  
OZTEK CORP. ANY REPRODUCTION IN  
PART OR AS A WHOLE WITHOUT THE  
WRITTEN PERMISSION OF OZTEK CORP IS  
PROHIBITED.

|                   |  |  |  |           |      |   |
|-------------------|--|--|--|-----------|------|---|
|                   |  | UNLESS OTHERWISE SPECIFIED:                              |  | NAME      | DATE |  <div>OZTEK CORP<br/>11 CONTINENTAL BLVD<br/>MERRIMACK, NH 03054</div> |
|                   |  | DIMENSIONS ARE IN MM                                     |  | DRAWN     | AGP  |   |
|                   |  | TOLERANCES:  |  | CHECKED   | KWE  |   |
|                   |  | MM INCH  |  | ENG APPR. |      |   |
|                   |  | .X ±.38 .020   |  | MFG APPR. |      |   |
|                   |  | .XX ±.12 .010  |  | Q.A.      |      | TITLE:<br>MUSTANG MECHANICAL<br>OUTLINE DRAWING   |
|                   |  | .XXX ±.005   |  | COMMENTS: |      |   |
|                   |  | USE MIN BEND RADII                                       |  |           |      | SIZE DWG. NO. REV<br><b>B</b> DWG-00032 <b>C</b>  |
|                   |  | INTERPRET GEOMETRIC<br>TOLERANCING PER: ASME Y14.5M-2009 |  |           |      |   |
|                   |  | MATERIAL   |  |           |      | SCALE: 1:2 WEIGHT: SHEET 2 OF 2   |
|                   |  | FINISH   |  |           |      |   |
| NEXT ASSY USED ON |  |  |  |           |      |   |
| APPLICATION       |  | DO NOT SCALE DRAWING                                     |  |           |      |   |