



RECOMMENDED MINIMUM CLEARANCES
(SEE O & M MANUAL FOR INSTALLATION DETAILS)

- NOTE 1) 36" [914] ALL 4 SIDES FOR MAINTENANCE.
- NOTE 2) 36" - 48" [914-1219] ALL 4 SIDES FOR AIR INTAKE.
- NOTE 3) 12-14 FT [3658-4267] FOR TOP HOT AIR EXHAUST.
- NOTE 4) LOAD BANK IS SUPPLIED WITH OUTDOOR WEATHERPROOF NEMA-3R-TYPE ENCLOSURE.

GENERAL NOTES:

- A. UNLESS OTHERWISE NOTED: 1. ALL DIMENSIONS ARE IN INCHES. EXCEPT "xxx" = mm.
- B. APPROX WEIGHT: 4500 - 5000 LBS [2041-2268 KG].
- C. SEE ELECTRICAL SCHEMATIC FOR LOAD CAPACITY (KW) RATINGS, VOLTAGE RATINGS, AND BLOWER MOTOR RATING (H.P.)

THIS DRAWING IS PROPERTY OF LOAD BANKS DIRECT AND SHALL REMAIN SO WHILE IN USERS POSSESSION. THE TECHNOLOGY SHOWN HERE IS STRICTLY PROPRIETARY AND IS NOT TO BE DISCLOSED TO ANY 3RD PARTY WITHOUT LOAD BANKS DIRECT PRIOR CONSENT.

Load Banks Direct
www.LoadBanksDirect.com

TECHNICAL LOAD BANK, 2000 THRU 3000KW, 36" FAN (WITH CHIMNEY HOOD)

DWG. NO. **LS2000-3000-OL**

REV. - SHEET 1 of 1

DATE 10/11/18

SIZE A

DRAWN BY JUF CHECKED BY MMP