



RECOMMENDED MINIMUM CLEARANCES
(SEE O & M MANUAL FOR INSTALLATION DETAILS)

- NOTE 1) 36" (914) ALL 4 SIDES FOR MAINTENANCE.
- NOTE 2) 36" - 48" (914-1219) ALL 4 SIDES FOR AIR INTAKE.
- NOTE 3) 12-14 FT (3658-4267) FOR TOP HOT AIR EXHAUST.
- NOTE 4) LOAD BANK IS SUPPLIED WITH OUTDOOR WEATHERPROOF NEMA-3R-TYPE ENCLOSURE.

GENERAL NOTES:

- A. UNLESS OTHERWISE NOTED: ALL DIMENSIONS ARE IN INCHES. EXCEPT "xxxx" = mm.
- B. APPROX WEIGHT: 1600 - 1900 LBS (726-862 KG)
- C. SEE ELECTRICAL SCHEMATIC FOR LOAD CAPACITY (KW) RATINGS, VOLTAGE RATINGS, AND BLOWER MOTOR RATING (H.P.)

THIS DRAWING IS PROPERTY OF LOAD BANKS DIRECT AND SHALL REMAIN SO WHILE IN USER'S POSSESSION. THE TECHNOLOGY SHOWN HERE IS STRICTLY PROPRIETARY AND IS NOT TO BE DISCLOSED TO ANY 3RD PARTY WITHOUT LOAD BANKS DIRECT PRIOR CONSENT.

		www.LoadBanksDirect.com	
TEXT	LOAD BANK, 800 THRU 1250KW (WITH GRAVITY HOOD)	REV.	SHEET
DWG. NO.	LS800-1250G-OL	DATE	3/26/13
DRAWN BY	JJF	CHECKD BY	MMP
SIZE			A