


RECOMMENDED MINIMUM CLEARANCES
 (SEE O & M MANUAL FOR INSTALLATION DETAILS)
 NOTE 1) 36" [914] ALL 4 SIDES FOR MAINTENANCE.
 NOTE 2) 36" - 48" [914-1219] ALL 4 SIDES FOR AIR INTAKE.
 NOTE 3) 12-14 FT [3658-4267] FOR TOP HOT AIR EXHAUST.

GENERAL NOTES:

- A. UNLESS OTHERWISE NOTED:
 1. ALL DIMENSIONS ARE IN INCHES.
 EXCEPT "xxxx" = mm.
- B. APPROX WEIGHT: 4800 LBS [2177 KG].
- C. SEE ELECTRICAL SCHEMATIC FOR LOAD CAPACITY (KW) RATINGS, VOLTAGE RATINGS, AND BLOWER MOTOR RATING (H.P.)

THIS DRAWING IS PROPERTY OF LOAD BANKS DIRECT AND SHALL REMAIN SO WHILE IN USER'S POSSESSION. THE TECHNOLOGY SHOWN HERE IS STRICTLY PROPRIETARY AND IS NOT TO BE DISCLOSED TO ANY 3RD PARTY WITHOUT LOAD BANKS DIRECT PRIOR CONSENT.

 Load Banks Direct www.LoadBanksDirect.com		DWG. NO.	REV.	SHEET
		LT3000-OL	-	1 of 1
TEXT	LOAD BANK, TRAILER READY			
DRAWN BY	CHECKD BY	DATE	SIZE	
JJF	MMP	9/18/19	A	