

MODEL	AMPERAGE	VOLTAGE	MOUNT	PERMANENT CONNECTION	TEMPORARY CONNECTION	OPTIONS
TATS	01 - 100A	1 -120/240V 1Ph	W - Wall	LL- Mechanical	M - Male Cam	A: Two Wire Auto Start
	02 - 200A	2 -120/240V 3Ph	P - Pad		F - Female Cam	B: Battery Charger Receptacle 20A DUPLEX 125V
	04 - 400A	3 -120/208V 3Ph	F - Flush		L - Mechanical	C: Battery Charger Receptacle 20A GFCI 125V
	06 - 600A	4 - 480V (No Neutral)	L - Leg Kit			D: Block Heater Receptacle 30A L5-30 125V
	08 - 800A	5 - 277/480V 3Ph				F: 50A Twist-Lock 125V/250V
	10 - 1000A					G: 100% Grounded
	12 - 1200A					H: SCADA Terminal Port I: Stainless Steel Construction M: Listed Monitoring Device N: Strip Heater & Thermostat O: Custom Listed Receptacles P: Surge Protection Device Q: Load Dump Receptacle R: Service Entrance Rated S: Special Request W: 4 Pole Switch Neutral Rotary Switch

**AUTOMATIC TRANSFER SWITCH DOCKING STATION**

Sample Part #: TATS-083W-LLM-ACD