

Tuff Box Series

50A-400A

PART NUMBER: TB-50AFT

PRODUCT DESCRIPTION:

Trystar Tuff Box

Feed Thru 50A 125/250V

UL1640 Listed

C(ETL) Listed

UL 50 Listed

NEMA 3R

INPUT:

50A California Style Flanged Inlet (125/250V)

OUTPUT:

50A California Style Receptacle (125/250V) for Feed Thru

6 x Duplex GFCI Receptacle (20A, 125V, NEMA 5-20R)

1 x L6-30 Receptacle (30A, 250V, NEMA L6-30R)

6 x 20 Amp 1P Branch Breaker

1 x 30 Amp 2P Branch Breaker

STANDARD FEATURES:

Aluminum Construction

Mounted on Heavy Duty Stackable Legs with Built-in Handles

Powder Coat Color: Customer Choice

UV Print: Customer Logo

Made in the USA

ADDITIONAL CONFIGURATIONS:

