

# Breaker Disconnect - 400A

Power Distribution Products



## APPLICATION RANGE

Trystar Breaker Disconnect

400A 600V

## STANDARD FEATURES


- NEMA 3R All Aluminum Construction
- Access Door with Breaker Viewing Window
- Removeable Gland Plate with Panel Mounts on Back of Panel
- Protective Caps on All Panel Mounts to Prevent Accidental Contact
- Mounted in Tilt and Roll Cage with Wheels
- Made in the USA

## CONFIGURATION

- Input
  - 1 Set of Male 16 Series Panel Mounts (BK,RD,BE,WT,GN)
- Output
  - 1 Set of Female 16 Series Panel Mounts (BK,RD,BE,WT,GN)
  - 1 x 400A Adjustable 3P Breaker (Acceptable for use up to 600V)

## LISTINGS

- UL1640 Listed
- C(ETL) Listed
- UL 50 Listed
- NEMA 3R





\*Images are representative, specific final design details may vary

# BREAKER DISCONNECT - 400A

## DIMENSIONS AND WEIGHTS



APPROXIMATE WEIGHT: 130 LBS.



\*Dimensions are representative, specific final design details may vary