

Breakout Panel - 4 x 100A

Power Distribution Products



APPLICATION RANGE

Trystar Breakout Panel


400A 600V

STANDARD FEATURES

- NEMA 3R All Aluminum Construction
- Access Door with Breaker Viewing Window
- Removeable Gland Plate with Panel Mounts on Back of Panel
- Protective Caps on All Panel Mounts to Prevent Accidental Contact
- Mounted in Tilt and Roll Cage with Wheels
- Made in the USA

CONFIGURATION

- Input
 - 1 Set of Male 16 Series Panel Mounts (BK,RD,BE,WT,GN)
- Output
 - 4 Set of Female 16 Series Panel Mounts (BK,RD,BE,WT,GN)
 - 4 x 100A Adjustable 3P Breaker (Acceptable for use up to 600V)



LISTINGS

- UL1640 Listed
- C(ETL) Listed
- UL 50 Listed
- NEMA 3R



*Images are representative, specific final design details may vary

Breakout Panel - 4 x 100A

DIMENSIONS AND WEIGHTS



APPROXIMATE WEIGHT: 130 LBS.



*Dimensions are representative, specific final design details may vary