



RECOMMENDED MINIMUM CLEARANCES
(SEE O & M MANUAL FOR INSTALLATION DETAILS)

NOTE 1) 36" [914] ALL 4 SIDES FOR MAINTENANCE.
NOTE 2) 36"- 48" [914-1219] ALL 4 SIDES FOR AIR INTAKE.
NOTE 3) 12-14 FT [3658-4267] FOR TOP HOT AIR EXHAUST.
NOTE 4) LOAD BANK IS SUPPLIED WITH OUTDOOR WEATHERPROOF NEMA-3R-TYPE ENCLOSURE.

THIS DRAWING IS PROPERTY OF LOAD BANKS DIRECT AND SHALL REMAIN SO WHILE IN USER'S POSSESSION. THE TECHNOLOGY SHOWN HERE IS STRICTLY PROPRIETARY AND IS NOT TO BE DISCLOSED TO ANY 3RD PARTY WITHOUT LOAD BANKS DIRECT PRIOR CONSENT.

REV 2: Revised pictorially. 18 3/4 dim locating bottom of relay compartment was 22 3/4. (3/6/15)
REV 1: Overall Length was 87 1/2 [2222]. (7/16/14)

GENERAL NOTES:

A. UNLESS OTHERWISE NOTED:
1. ALL DIMENSIONS ARE IN INCHES. EXCEPT "[xxx]" = mm.

B. APPROX WEIGHT: 2600 - 3000 LBS [1179-1361 KG].

C. SEE ELECTRICAL SCHEMATIC FOR LOAD CAPACITY (KW) RATINGS, VOLTAGE RATINGS, AND BLOWER MOTOR RATING (H.P.)

LOAD BANK, TRAILER READY (1000 THRU 1500 KW)			
DWG. NO.	REV.	SHEET	
LT1000-1500-OL	2	1 of 1	
DRAWN BY	CHKD BY	DATE	SIZE
JJF	MMP	3/10/14	A