




TRYSTAR®

## MTSTB Manual Transfer Switch Triple Breaker





## MTSTB Series



### Manual Transfer Switch Triple Breaker

MALE AND FEMALE CAM LOKS FOR CONNECTION OF TEMPORARY GENERATOR AND LOAD BANK, LUGS FOR CONNECTION OF PERMANENT GENERATOR

CABINET IS WALL MOUNTED AND IS AVAILABLE IN TYPE 3R PAINTED ENCLOSURE OR TYPE 3R 316 STAINLESS STEEL

AVAILABLE WITH PILOT LIGHT INDICATORS FOR VOLTAGE PRESENT FOR ALL THREE PHASES

TRAPPED KEY INTERLOCKED PERMANENT GEN BREAKER AND TEMPORARY GEN BREAKER, THIRD BREAKER FOR LOAD BANK CONNECTION WITH SHUNT TRIP FOR LOAD DUMP

UL 508A Listed:

100-800 Amps, up to 600 Volts.

CSA C22.2#178.1:2014 Ed.3+U1;U2



### Features

TYPE 3R ENCLOSURE ANSI 61 GRAY

TYPE 3RSS 316 STAINLESS STEEL ENCLOSURE

OPTIONAL PILOT LIGHT INDICATION FOR VOLTAGE PRESENT

RATED THROUGH 600VAC 3 OR 4 WIRE

BUS BAR SIZED 1000A/SQ INCH, FULLY RATED

100% TESTED AT FULL VOLTAGE

PHASE REVERSAL PROTECTION RELAY INCLUDED

3 WIRE AUTO START TERMINALS INCLUDED

DOOR PREVENTS CONNECTION OF GEN CAM LOKS AND LOAD BANK CAM LOKS AT THE SAME TIME.



TRYSTAR<sup>®</sup>