

15KVA Transformer

15KVA

PART NUMBER: TF-15KVA480/208SDD-CG/D

PRODUCT DESCRIPTION:

15KVA Trystar Portable Dolly Cart Transformer

480V:208Y/120V Step Down

UL 1640 Listed

C(ETL) Listed

UL 50 Listed

NEMA 3R

PRIMARY SIDE:

4/4 Type W Hardwire Input 15FT

20A 3P Primary Side Transformer Circuit Breaker

SECONDARY SIDE:

50A 3P 240V Secondary Side Transformer Circuit Breaker

9 x 20A 120V Duplex Receptacles

9 x 20A 240V 1P GFCI Circuit Breakers

STANDARD FEATURES:

All Aluminum Corrosion Resistant Construction

Steel Construction Dolly

Lift Eye and Fork Pockets

Powder Coat Color: Customer Choice

UV Print: Customer Logo

Made in the USA



***MULTIPLE CONFIGURATIONS: CONTACT TRYSTAR FOR MORE INFORMATION**