

Tuff Panel Series

100A-400A

PART NUMBER: TP-2FTLC-10P

PRODUCT DESCRIPTION:

Trystar Tuff Panel Camlok Feed Thru

Camlok Input 400A 208Y/120V

UL 1640 Listed

C(ETL) Listed

UL 50 Listed

NEMA 3R

INPUT:

1 Set of Male 16 Series Panel Mounts (BK, RD, BE, WT, GN)

OUTPUT:

1 Set of 16 Series Female Panel Mounts for Feed Thru

(BK, RD, BE, WT, GN)

10 x 20A 120Y/280V 3P Wetguard L21-20 Quad Receptacles

30 x 20A 120V 1P Branch Breakers

STANDARD FEATURES:

All Aluminum Corrosion Resistant Construction

Access Door with Breaker Viewing Window

Phase Indicator Lights Included

Pad Lockable Front Door

Removable Gland Plate with Panel Mounts on Back of Panel

Protective Caps on all Panel Mounts to Prevent Accidental Contact

Mounted on Heavy Duty Aluminum Legs in Cage

Powder Coat Color: Customer Choice

UV Print: Customer Logo

Made in the USA



***MULTIPLE CONFIGURATIONS: CONTACT TRYSTAR FOR MORE INFORMATION**