

# 800A I-LINE

Portable Power Distribution



## APPLICATION RANGE

800A Trystar Vertical I-Line

Panel Rated for 600V

## STANDARD FEATURES


- I-Line includes 27" Section of Breaker Space
- NEMA 3R All Aluminum Construction
- Changeable Gland Plates
- Heavy Duty Cage with Forklift Pockets
- Metal Casters with Industrial Grade Floor Locks
- Protective Caps on All Panel Mounts to Prevent Accidental Contact
- Made in the USA

## CONFIGURATION

- Input
  - 2 Sets of Male 16 Series Panel Mount Input (BK, RD, BE, WT, GN)
- Output
  - 4 X 70-250A 600V Adjustable Breakers
  - 4 Sets of Female 16 Series Panel Mount Outputs BK, RD, BE, WT, GN)

## LISTINGS

- UL1640 Listed
- C(ETL) Listed
- UL 50 Listed
- NEMA 3R




\*Images are representative, specific final design details may vary

# 800A I-LINE

## DIMENSIONS AND WEIGHTS



APPROXIMATE WEIGHT: 1,500 LBS.



\*Dimensions are representative, specific final design details may vary