800A Power Distribution Panel

Portable Power Distribution



APPLICATION RANGE

800A Trystar Vertical Power Distribution

Panel Panel Rated for 600V

STANDARD FEATURES


- · Panel includes 27" Section of Breaker Space
- NEMA 3R All Aluminum Construction
- Changeable Gland Plates
- · Heavy Duty Cage with Forklift Pockets
- · Metal Casters with Industrial Grade Floor Locks
- Protective Caps on All Panel Mounts to Prevent Accidental Contact
- Made in the USA

CONFIGURATION

- Input
 - 2 Sets of Male 16 Series Panel Mount Input (BK,RD,BE,WT,GN)
- Output
 - ° 4 X 70-250A 600V Adjustable Breakers
 - 4 Sets of Female 16 Series Panel Mount Outputs BK, RD, BE, WT, GN)

LISTINGS

- UL1640 Listed
- · C(ETL) Listed
- UL 50 Listed
- NEMA 3R




*Images are representative, specific final design details may vary


DIMENSIONS AND WEIGHTS



APPROXIMATE WEIGHT: 1,500 LBS.



53 1/4"



*Dimensions are representative, specific final design details may vary