



TRYSTAR®

## LP Equipment Protection

100kW - 1000kW Portable Load Banks



**Protective Shipping Solutions for LP Portable Load Banks**

Trystar offers a complete line of travel solutions for the LP line of Portable Load Banks from 100kW to 1000kW. Whether you just need a cage for equipment protection during shipment, or would like a permanently installed protective frame for better overall handling and durability, Trystar has the right solution.

Perfect for service and rental companies, the LP travel solutions provide equipment shipping protection while simplifying the handling of the load bank. With multiple lifting provisions and tie down eyelets, the Trystar Protective Shipping Cages are the smart way to transport your load banks.

- Heavy Duty Cages, Frames and Cases for Maximum Protection
- Cage has Fork Pockets on all sides
- Roll out and fixed frame designs
- Cages allow for load bank operation without removing

Load Bank	Case	Cage	Frame
LC100/LP100	√		
LP125	√		
LP300-700		√	√
LP800-1000		√	√



**Case** - rugged black PVC laminate sides with aluminum edges, steel ball corners, foamed lined, cable storage area

**Cage** - Powder coated tube steel, stackable, storage pocket

**Frame** - Heavy duty galvanized construction



Shown above: LP100 with LP100-CASE

Roll Out	Fixed
<p><b>Trystar Cages</b></p> <ul style="list-style-type: none"> <li>• Heavy Duty powder coated tube steel construction provides maximum protection for your critical test equipment</li> <li>• Integrated ramp for easy roll-on/ roll-out</li> <li>• Fork lift channels all sides and eye bolts for ease of handling</li> <li>• Provides recessed component protection keeping front operator controls and Cam-Loks safe during transport</li> <li>• (2) Rack Straps and bumpers secure the load bank for shipping</li> <li>• Designed to be operated in Cage, Cam-Loks and Control Panel easily accessible (shipping straps must be removed)</li> </ul>	<p><b>Trystar Frames</b></p> <ul style="list-style-type: none"> <li>• Heavy duty 8 gauge frame provides maximum protection for your critical test equipment</li> <li>• Protective framework remains in place at all times (nothing has to be removed prior to load testing)</li> <li>• Provides recessed component protection to keep front controls and cam locks safe during transport</li> <li>• Bolt together construction allows for easy installation when adding to your existing Trystar LP style load bank</li> <li>• Multiple lifting provisions are available from either the top center eye or the four eyelets in the top corners</li> <li>• Twelve tie down eyelets are available for safely transporting your load bank to the job site</li> <li>• Standard mill galvanized finish offers corrosion resistance and durability (optional painted finish available)</li> </ul>
<p><b>Trystar Cases</b></p> <ul style="list-style-type: none"> <li>• Rugged Black PVC Laminate sides</li> <li>• Aluminum cornering extrusion</li> <li>• Steel ball corners</li> <li>• Foam lined</li> <li>• 3.5” casters, two are lockable</li> <li>• Pull over removable lid secured with 4 heavy duty recessed latches &amp; handles</li> <li>• Cable storage in case base</li> </ul>	

**Operator Controls and Cam-Loks are easily accessible**



**Roll on / Roll out Design Can be operated without removing**



**Protect your load test assets with convenient cases, roll out cages or fixed shipping frames!**



TRYSTAR<sup>®</sup>