



OPERATOR REMOTE CONTROL UNIT FOR DUAL VOLTAGE LOAD BANKS



OPERATOR REMOTE CONTROL UNIT FOR SINGLE VOLTAGE LOAD BANKS



RECOMMENDED MINIMUM CLEARANCES (SEE O & M MANUAL FOR INSTALLATION DETAILS)

- NOTE 1) 36" [914] ALL 4 SIDES FOR MAINTENANCE.
- NOTE 2) 36"- 48" [914-1219] ALL 4 SIDES FOR AIR INTAKE.
- NOTE 3) 12-14 FT [3658-4267] FOR TOP HOT AIR EXHAUST.
- NOTE 4) LOAD BANK IS SUPPLIED WITH OUTDOOR WEATHERPROOF NEMA-3R-TYPE ENCLOSURE.

THIS DRAWING IS PROPERTY OF LOAD BANKS DIRECT AND SHALL REMAIN SO WHILE IN USER'S POSSESSION. THE TECHNOLOGY SHOWN HERE IS STRICTLY PROPRIETARY AND IS NOT TO BE DISCLOSED TO ANY 3RD PARTY WITHOUT LOAD BANKS DIRECT PRIOR CONSENT.

REV 2: REV TERMINAL COMPARTMENT DIM'S.
REV 1: DWG NO & RATING WAS LS400-800.

GENERAL NOTES:

- A. UNLESS OTHERWISE NOTED:
1. ALL DIMENSIONS ARE IN INCHES. EXCEPT "[xxx]" = mm.
- B. APPROX WEIGHT: 1100 - 1400 LBS [499-635 KG].
- C. SEE ELECTRICAL SCHEMATIC FOR LOAD CAPACITY (KW) RATINGS, VOLTAGE RATINGS, AND BLOWER MOTOR RATING (H.P.)



LOAD BANK, 250 THRU 800KW

DWG. NO. LS250-800-OL		REV. 2	SHEET 1 of 1	
DRAWN BY JJF	CHKD BY MMP	DATE 2/7/13	SIZE A	