



RECOMMENDED MINIMUM CLEARANCES
 (SEE O & M MANUAL FOR INSTALLATION DETAILS)

NOTE 1) 36" [914] ALL 4 SIDES FOR MAINTENANCE.
 NOTE 2) 36" - 48" [914-1219] ALL 4 SIDES FOR AIR INTAKE.
 NOTE 3) 12-14 FT [3658-4267] FOR TOP HOT AIR EXHAUST.

THIS DRAWING IS PROPERTY OF LOAD BANKS DIRECT AND SHALL REMAIN SO WHILE IN USER'S POSSESSION. THE TECHNOLOGY SHOWN HERE IS STRICTLY PROPRIETARY AND IS NOT TO BE DISCLOSED TO ANY 3RD PARTY WITHOUT LOAD BANKS DIRECT PRIOR CONSENT.

GENERAL NOTES:

A. UNLESS OTHERWISE NOTED:
 1. ALL DIMENSIONS ARE IN INCHES. EXCEPT "[xxx]" = mm.

B. APPROX WEIGHT: 4800 LBS [2177 KG].

C. SEE ELECTRICAL SCHEMATIC FOR LOAD CAPACITY (KW) RATINGS, VOLTAGE RATINGS, AND BLOWER MOTOR RATING (H.P.)

LOAD BANK, TRAILER READY			
DWG. NO.	REV.	SHEET	
LT3000-OL	-	1 of 1	
DRAWN BY	CHKD BY	DATE	SIZE
JJF	MMP	9/18/19	A